



Dynalite Signal Dimmer Controllers

DDBC120-DALI

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

Product data

Mechanical and Housing	
Net Weight (Piece)	203.000 g
Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes
Remarks	Please download the Lighting – Product Data Sheet for more information and ordering options
Ambient temperature range	0 to +40 °C
Product Data	
Order product name	DDBC120-DALI

Full product name	DDBC120-DALI
Full EOC	871869688704200
Order code	913703685109
Material no. (12 NC)	913703685109
Local order code	DDBC120DALIV4
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696887042
Numerator – packs per outer box	1
EAN/UPC – Case	8718696894040

Dynalite Signal Dimmer Controllers

Dimensional drawing

