



Electronic semi-parallel ignitor for HID lamp circuits

SN 58

HID ignitors for semi-parallel systems

Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Wiring	
Connector Type	Screw

Temperature	
T-Case Maximum (Max)	90 °C

Mechanical and Housing	
Housing	Akulon S223
Net Weight (Piece)	0.049 kg


Approval and Application	
Approval Marks	CE marking ENEC certificate

Ambient temperature range	-20 °C to 85 °C
---------------------------	-----------------

Product Data	
Order product name	SN 58
Full product name	SN 58
Full product code	697013372881900
Order code	72881900
Material Nr. (12NC)	913710010513
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6970133728819
Numerator - Packs per outer box	48
EAN/UPC - Case	6970133728826

Electronic semi-parallel ignitor for HID lamp circuits

Dimensional drawing



Product	C1	A1	A2	B1
SN 58	38.5 mm	85.5 mm	65.0 mm	41.5 mm

