



# Electronic semi-parallel ignitor for HID lamp circuits

## SN 56

HID ignitors for semi-parallel systems


### Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Wiring	
Connector Type	Screw
Temperature	
T-Case Maximum (Max)	60 °C
Mechanical and Housing	
Housing	Akulon S223
Net Weight (Piece)	0.079 kg
Approval and Application	
Approval Marks	CE marking

Ambient temperature range	-20 °C to 55 °C
Product Data	
Order product name	SN 56
Full product name	SN 56
Full product code	697013372885700
Order code	72885700
Material Nr. (12NC)	913710010713
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6970133728857
Numerator - Packs per outer box	20
EAN/UPC - Case	6970133728864

# Electronic semi-parallel ignitor for HID lamp circuits

## Dimensional drawing



Product	C1	A1	A2	B1
SN 56	38.5 mm	114.5 mm	95.0 mm	41.5 mm

