



Electronic parallel ignitor for HID lamp circuits

SI 51 Plus

HID ignitors for parallel systems


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Wiring	
Connector Type	Screw
Temperature	
T-Case Maximum (Max)	80 °C
Mechanical and Housing	
Housing	Akulon S223
Net Weight (Piece)	0.049 kg
Approval and Application	
Approval Marks	CE marking ENEC certificate

Ambient temperature range	-20 °C to 75 °C
Product Data	
Order product name	SI 51 Plus
Full product name	SI 51 Plus
Full product code	697013372887100
Order code	913710011113
Material Nr. (12NC)	913710011113
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6970133728871
Numerator - Packs per outer box	48
EAN/UPC - Case	6970133728888

Electronic parallel ignitor for HID lamp circuits

Dimensional drawing



Product	C1	A1	A2	B1	D1
SI 51 Plus	38.5 mm	85.5 mm	65.0 mm	41.5 mm	4.3 mm

