



# Electronic series ignitor for HID lamp circuits

## SU 52

HID ignitors for series systems


### Product data

Operating and Electrical	
Input Voltage	380-420 V
Input Frequency	50 to 60 Hz
Wiring	
Connector Type	Screw
Temperature	
T-Case Maximum (Max)	105 °C
Mechanical and Housing	
Housing	PC UL94V-2
Net Weight (Piece)	0.080 kg
Approval and Application	
Approval Marks	China Quality Certificate CB Certificate

Product Data	
Order product name	SU 52
Full product name	SU 52
Full product code	697013372891800
Order code	913710011313
Material Nr. (12NC)	913710011313
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6970133728918
Numerator - Packs per outer box	10
EAN/UPC - Case	6970133728925

## Electronic series ignitor for HID lamp circuits

### Dimensional drawing



Product	C1	A1	A2	B1	D1
SU 52	50 mm	90 mm	69 mm	55 mm	4.3 mm

