

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 250L 302I


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name	BSN 250L 302I
Input Voltage	230 V	Full product code	871016303131630
Line Frequency	50 Hz	Order code	913710102850
Input Frequency	50 Hz	Material Nr. (12NC)	913710102850
Wiring		Numerator - Quantity Per Pack	1
Connector Type	Screw	EAN/UPC - Product/Case	8710163148366
Mechanical and Housing		Numerator - Packs per outer box	6
Net Weight (Piece)	2.700 kg	EAN/UPC - Case	8710163032306
Product Data			
Order product name	BSN 250L 302I		

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 250L 302I	6.3 mm	64.5 mm	150.0 mm	129.0 mm	72.5 mm

