



HID-High Power ballasts for SON/MH lamps

BSN 1000L 3021

Impregnated (HID standard) electromagnetic ballasts, of copper/iron construction, for use in combination with an external ignitor, for HID lamps

Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz

Wiring	
Connector Type	Screw


Mechanical and Housing	
Net Weight (Piece)	8.700 kg

Approval and Application	
Approval Marks	CE marking CCC certificate

Product Data	
Order product name	BSN 1000L 3021
Full product name	BSN 1000L 3021
Full product code	697480505005500
Order code	913710106742
Material Nr. (12NC)	913710106742
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6974805050055
Numerator - Packs per outer box	1
EAN/UPC - Case	6974805050062

HID-High Power ballasts for SON/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 1000L 302I	7 mm	102.0 mm	183 mm	134.5 mm	117.0 mm

