



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 150L 300I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz

Wiring	
Connector Type	Screw


Mechanical and Housing	
Net Weight (Piece)	1.850 kg

Approval and Application	
Approval Marks	CCC certificate

Product Data	
Order product name	BSN 150L 300I TS
Full product name	BSN 150L 300I TS
Full product code	697480505007900
Order code	913710109142
Material Nr. (12NC)	913710109142
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6974805050079
Numerator - Packs per outer box	6
EAN/UPC - Case	6974805050086

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 150L 300I TS	6.2 mm	64.5 mm	125.0 mm	110 mm	75.5 mm

