

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 250L 300I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.


Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Mechanical and Housing	
Net Weight (Piece)	2.700 kg
Approval and Application	
Approval Marks	CE marking CCC certificate

Product Data	
Order product name	BSN 250L 300I TS
Full product name	BSN 250L 300I TS
Full product code	697480505079600
Order code	913710109342
Material Nr. (12NC)	913710109342
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6974805050796
Numerator - Packs per outer box	6
EAN/UPC - Case	6974805050802

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 250L 300I TS	6.2 mm	64.5 mm	150.0 mm	135 mm	75.5 mm

