

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSNE 400L 300I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.


Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Mechanical and Housing	
Net Weight (Piece)	4.500 kg
Approval and Application	
Approval Marks	CE marking CCC certificate

Product Data	
Order product name	BSNE 400L 300I TS
Full product name	BSNE 400L 300I TS
Full product code	697480505037600
Order code	913713019559
Material Nr. (12NC)	913713019559
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6974805050376
Numerator - Packs per outer box	4
EAN/UPC - Case	6974805050383

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSNE 400L 300I TS	6.3 mm	82 mm	165.0 mm	144 mm	96.0 mm

