



HF-Performer III for TL5 lamps

HF-P 154/155 TL5 HO/PLL III 220-240V IDC

HF-Performer III TL5 is a sustainable, slim and high-frequency electronic ballast for TL5 and TL5 Eco fluorescent lamps. It is ideal for applications where high energy efficiency is required. The HF-Performer III range has a robust design, meets all relevant international safety and performance standards and is energy-efficient (CELMA EEI A2 BAT).

Product data


| Operating and Electrical | | T-Case maximum (max.) | 80 °C |
|--|---|---------------------------|---|
| Input Voltage | 220 to 240 V | | |
| Line Frequency | 50 to 60 Hz | Mechanical and Housing | |
| Input frequency | 50 to 60 Hz | Housing | L360x30x22 |
| Inrush current width | 0.25 ms | Ingress protection code | IP20 [Finger-protected] |
| Inrush current peak (max.) | 24 A | Net Weight (Piece) | 0.252 kg |
| Number of products on MCB (16 A type B) (nom.) | 28 | Approval and Application | |
| Wiring | | Energy efficiency index | A2 BAT |
| Connector type input terminals | WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring] | Safety standard | IEC 61347-2-3 |
| Connector type output terminals | WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring] | Environmental standard | ISO 14001 |
| | | Approval marks | CE marking ENEC certificate VDE-EMV certificate |
| Temperature | | CE mark | Yes |
| T-case lifetime (nom.) | 80 °C | Ambient temperature range | -25°C to 60°C |
| | | Product Data | |
| | | Order product name | HF-P 154/155 TL5 HO/PLL III 220-240V IDC |
| | | Full product name | HF-P 154/155 TL5 HO/PLL III 220-240V IDC |
| | | Full EOC | 872790086348200 |

HF-Performer III for TL5 lamps

| | |
|-------------------------------|----------------|
| Order code | 913713028266 |
| Material no. (12 NC) | 913713028266 |
| Local order code | HFP154TL5HOIII |
| Numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 8711500998217 |

| | |
|---------------------------------|---------------|
| Numerator – packs per outer box | 12 |
| EAN/UPC – Case | 8727900863482 |

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 |
|---|--------|---------|----------|----------|---------|
| HF-P 154/155 TL5 HO/PLL III 220-240V IDC | 4.2 mm | 22.0 mm | 360.0 mm | 350.0 mm | 30.0 mm |

