



HF-Performer III for TL5 lamps

HF-P 154/155 TL5 HO/PLL III 220-240V IDC

HF-Performer III TL5 is a sustainable, slim and high-frequency electronic ballast for TL5 and TL5 Eco fluorescent lamps. It is ideal for applications where high energy efficiency is required. The HF-Performer III range has a robust design, meets all relevant international safety and performance standards and is energy-efficient (CELMA EEI A2 BAT).

Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Inrush Current Width	0.25 ms
Inrush Current Peak (Max)	24 A
Number of Products on MCB (16A Type B) (Nom)	28
Wiring	
Connector Type Input Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Connector Type Output Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Temperature	
T-Case Lifetime (Nom)	80 °C


T-Case Maximum (Max)	80 °C
Mechanical and Housing	
Housing	L360x30x22
Ingress protection code	IP20 [Finger-protected]
Net Weight (Piece)	0.252 kg
Approval and Application	
Energy Efficiency Index	A2 BAT
Safety Standard	IEC 61347-2-3
Environmental Standard	ISO 14001
Approval Marks	CE marking ENEC certificate VDE-EMV certificate
CE mark	Yes
Ambient temperature range	-25 °C to 60 °C
Product Data	
Order product name	HF-P 154/155 TL5 HO/PLL III 220-240V IDC
Full product name	HF-P 154/155 TL5 HO/PLL III 220-240V IDC
Full product code	872790086348200

HF-Performer III for TL5 lamps

Order code	913713028266
Material Nr. (12NC)	913713028266
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500998217

Numerator - Packs per outer box	12
EAN/UPC - Case	8727900863482

Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-P 154/155 TL5 HO/PLL III 220-240V IDC	4.2 mm	22.0 mm	360.0 mm	350.0 mm	30.0 mm

