



# HF-Performer III for TL5 lamps

## HF-P 254/255 TL5 HO/PLL III 220-240V IDC

HF-Performer III TL5 is a sustainable, slim and high-frequency electronic ballast for TL5 and TL5 Eco fluorescent lamps. It is ideal for applications where high energy efficiency is required. The HF-Performer III range has a robust design, meets all relevant international safety and performance standards and is energy-efficient (CELMA EEI A2 BAT).

### Product data


Operating and Electrical		T-Case Maximum (Max)	80 °C
Input Voltage	220 to 240 V	<b>Mechanical and Housing</b>	
Line Frequency	50 to 60 Hz	Housing	L360x30x22
Input Frequency	50 to 60 Hz	Ingress protection code	IP20 [Finger-protected]
Inrush Current Width	0.35 ms	Net Weight (Piece)	0.280 kg
Inrush Current Peak (Max)	31 A	<b>Approval and Application</b>	
Number of Products on MCB (16A Type B) (Nom)	12	Energy Efficiency Index	A2 BAT
<b>Wiring</b>		Safety Standard	IEC 61347-2-3
Connector Type Input Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]	Environmental Standard	ISO 14001
Connector Type Output Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]	Approval Marks	CE marking ENEC certificate VDE-EMV certificate
<b>Temperature</b>		CE mark	Yes
T-Case Lifetime (Nom)	80 °C	Ambient temperature range	-25 °C to 60 °C
		<b>Product Data</b>	
		Order product name	HF-P 254/255 TL5 HO/PLL III 220-240V IDC
		Full product name	HF-P 254/255 TL5 HO/PLL III 220-240V IDC
		Full product code	872790086351200

## HF-Performer III for TL5 lamps

Order code	913713028366
Material Nr. (12NC)	913713028366
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500998224

Numerator - Packs per outer box	12
EAN/UPC - Case	8727900863512

### Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-P 254/255 TL5 HO/PLL III 220-240V IDC	4.2 mm	22.0 mm	360.0 mm	350.0 mm	30.0 mm

