



HF-Selectalume II for TL-D lamps

HF-S 3/4 18 TL-D II 220-240V 50/60Hz

HF-Selectalume II TL-D is the most cost-effective, reliable and outstanding solution for fluorescent lamps. These ballasts are part of an overall high-efficiency lighting system that may help you or your customers to achieve any international or local energy code you need to comply with. HF-Selectalume II TL-D ballasts are the ideal choice for a broad range of new construction and retrofit applications within the commercial sector, including general surface mounting or office lighting, parking garages, warehouses, waterproof and other applications. The ballast is primarily designed for Indoor application. For outdoor application, the luminaire should be minimum Classland need to be sufficiently protected against water & dust. The installation should also be guard against any lightening surge or any other necessary electrical protection as deemed in such typical installation & application.

Product data


Operating and Electrical		Connector Type Output Terminals	
Input Voltage	220 to 240 V	WAGO 744 connector [Suitable for manual wiring]	
Line Frequency	50 to 60 Hz	Temperature	
Input Frequency	50 to 60 Hz	T-Case Lifetime (Nom)	75 °C
Earth Leakage Current (Max)	0.5 mA	T-Case Maximum (Max)	75 °C
Inrush Current Width	0.35 ms	Mechanical and Housing	
Inrush Current Peak (Max)	18 A	Housing	L 280x39x28
Number of Products on MCB (16A Type B) (Nom)	28	Ingress protection code	IP20 [Finger-protected]
Wiring		Net Weight (Piece)	0.228 kg
Connector Type Input Terminals	WAGO 744 connector	Approval and Application	
		Energy Efficiency Index	A2/A2 BAT

HF-Selectalume II for TL-D lamps

Approval Marks	F-Marking CE marking ENEC certificate CCC certificate C-Tick certificate PSB certification TISI marking SIRIM approval CB Certificate CCC certificate VDE-EMV certificate
CE mark	Yes
Ambient temperature range	-20 °C to 50 °C
Product Data	
Order product name	HF-S 3/4 18 TL-D II 220-240V 50/60Hz
Full product name	HF-S 3/4 18 TL-D II 220-240V 50/60Hz

Full product code	872790090555700
Order code	913713032666
Material Nr. (12NC)	913713032666
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500999320
Numerator - Packs per outer box	10
EAN/UPC - Case	8727900905557

Dimensional drawing



Product	HF-S 3/4 18 TL-D II 220-240V 50/60Hz
----------------	--------------------------------------

Product	A1	B1	C1	A2	B2	D1
HF-S 3/4 18 TL-D II 220-240V 50/60Hz	280 mm	39 mm	28 mm	265 mm		4.2 mm

