



HF-Performer III for TL5 lamps

HF-P 280 TL5/PL-L III 220-240V 50/60Hz

HF-Performer III TL5 is a sustainable, slim and high-frequency electronic ballast for TL5 and TL5 Eco fluorescent lamps. It is ideal for applications where high energy efficiency is required. The HF-Performer III range has a robust design, meets all relevant international safety and performance standards and is energy-efficient (CELMA EEI A2 BAT).

Product data


Operating and Electrical		T-Case Maximum (Max)	85 °C
Input Voltage	220 to 240 V	Mechanical and Housing	
Line Frequency	50 to 60 Hz	Housing	L 425x30x21
Input Frequency	50 to 60 Hz	Ingress protection code	IP20 [Finger-protected]
Inrush Current Width	0.38 ms	Net Weight (Piece)	0.360 kg
Inrush Current Peak (Max)	35 A	Approval and Application	
Number of Products on MCB (16A Type B) (Nom)	8	Energy Efficiency Index	A2 BAT
Wiring		Safety Standard	IEC 61347-2-3
Connector Type Input Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]	Environmental Standard	ISO 14001
Connector Type Output Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]	Approval Marks	CE marking ENEC certificate VDE-EMV certificate
Temperature		Ambient temperature range	-25 °C to 60 °C
T-Case Lifetime (Nom)	85 °C	Product Data	
		Order product name	HF-P 280 TL5/PL-L III 220-240V 50/60Hz
		Full product name	HF-P 280 TL5/PL-L III 220-240V 50/60Hz
		Full product code	872790095230800
		Order code	913713034366

HF-Performer III for TL5 lamps

Material Nr. (12NC)	913713034366
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900952308
Numerator - Packs per outer box	12

EAN/UPC - Case	8727900952315
----------------	---------------

Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-P 280 TL5/PL-L III 220-240V 50/60Hz	4.2 mm	21.0 mm	425.0 mm	415.0 mm	30.0 mm

