



HID-High Power ballasts for MH lamps

BMH 2000L 2114

The HID High-Power ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical	
Input Voltage	400 V

Wiring	
Connector Type	Screw

Mechanical and Housing	
Net Weight (Piece)	14.100 kg


Full product name	BMH 2000L 2114
Full product code	697480505039000
Order code	913713201767
Material Nr. (12NC)	913713201767
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6974805050390
Numerator - Packs per outer box	1
EAN/UPC - Case	6974805050406

Product Data

Order product name	BMH 2000L 2114
--------------------	----------------

HID-High Power ballasts for MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BMH 2000L 2114	7 mm	102 mm	215.0 mm	181.0 mm	117.0 mm

