



# SlimPerform Batten

## BN310P LED92/830 PSU DA L1150 WH

SlimPerform Batten, 56 W, 9200 lm, 3000 K

Lighting plays a different role in every application. Some require latest-generation solutions with high light quality and connectivity; others just simple functionality. But whether for retail or industrial applications, you always need a combination of quality, performance, and flexibility. Get to know SlimPerform. The Batten LED luminaire where all these benefits come together. Putting the new lighting trend in your company.

### Warnings and Safety

- 5-year warranty

### Product data

General Information		Power Consumption	
Light source replaceable	No	Power Factor (Fraction)	0.92
Driver included	Yes	Connection	Connection unit 3-pole
Value ladder	Performance	Cable	Cable 0.25 m with connector 3-pole
Light Technical		Protection class IEC	Safety class I
Luminous Flux	9,200 lm	Controls and Dimming	
Correlated Color Temperature (Nom)	3000 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	164.28571428571428 lm/W	Driver/power unit/transformer	Power supply unit (On/Off)
Color rendering index (CRI)	>80	Control interface	-
Operating and Electrical		Constant light output	No
Input Voltage	220 to 240 V	Maximum dim level	Not applicable
Line Frequency	50 or 60 Hz	Mechanical and Housing	
Inrush current	28.2 A	Housing Material	Aluminum
Inrush time	0.135 ms	Housing Color	White

# SlimPerform Batten

Mounting device	Mounting bracket
Overall length	1,132 mm
Overall width	59 mm
Overall height	82 mm
Dimensions (Height x Width x Depth)	82 x 59 x 1132 mm
Ingress protection code	IP20 [Finger-protected]
Net Weight (Piece)	1.430 kg

## Approval and Application

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

## Product Data

Order product name	BN310P LED92/830 PSU DA L1150 WH
Full product name	BN310P LED92/830 PSU DA L1150 WH
Order code	919406020841
Material Nr. (12NC)	919406020841
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400003630
Numerator - Packs per outer box	5
EAN/UPC - Case	17894400003637

## Dimensional drawing

