



# SlimPerform Batten

## BN310P LED160/865 PSU MB EL L1700 WH

SlimPerform Batten, 101 W, 16500 lm, 6500 K

Lighting plays a different role in every application. Some require latest-generation solutions with high light quality and connectivity; others just simple functionality. But whether for retail or industrial applications, you always need a combination of quality, performance, and flexibility. Get to know SlimPerform. The Batten LED luminaire where all these benefits come together. Putting the new lighting trend in your company.

### Warnings and Safety

- 5-year warranty

### Product data

General Information		Power Consumption	
Light source replaceable	No	Power Consumption	101 W
Driver included	Yes	Power Factor (Fraction)	0.92
Value ladder	Performance	Connection	Connection unit 3-pole
		Cable	Cable 0.25 m with connector 3-pole
		Protection class IEC	Safety class I
Light Technical		Controls and Dimming	
Luminous Flux	16,500 lm	Dimmable	No
Correlated Color Temperature (Nom)	6500 K	Driver/power unit/transformer	Power supply unit (On/Off)
Luminous Efficacy (rated) (Nom)	163.36633663366337 lm/W	Control interface	-
Color rendering index (CRI)	>80	Constant light output	No
		Maximum dim level	Not applicable
Operating and Electrical		Mechanical and Housing	
Input Voltage	220 to 240 V	Housing Material	Aluminum
Line Frequency	50 or 60 Hz	Housing Color	White
Inrush current	47.4 A		
Inrush time	0.135 ms		

# SlimPerform Batten

Mounting device	Mounting bracket
Overall length	1,691 mm
Overall width	59 mm
Overall height	82 mm
Dimensions (Height x Width x Depth)	82 x 59 x 1691 mm
Ingress protection code	IP23 [Finger-protected, rain/spray-proof]
Net Weight (Piece)	2.700 kg

## Approval and Application

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

## Product Data

Order product name	BN310P LED160/865 PSU MB EL L1700 WH
Full product name	BN310P LED160/865 PSU MB EL L1700 WH
Order code	919406021361
Material Nr. (12NC)	919406021361
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400002893
Numerator - Packs per outer box	5
EAN/UPC - Case	17894400002890

## Dimensional drawing

