



SlimPerform Batten

BN310P LED200/865 SRD H4 HRO L1700 WH

SlimPerform Batten, 129 W, 20000 lm, 6500 K, InterAct Pro

Lighting plays a different role in every application. Some require latest-generation solutions with high light quality and connectivity; others just simple functionality. But whether for retail or industrial applications, you always need a combination of quality, performance, and flexibility. Get to know SlimPerform. The Batten LED luminaire where all these benefits come together. Putting the new lighting trend in your company.

Warnings and Safety

- 5-year warranty

Product data

General Information		Power Consumption	
Light source replaceable	No	Power Factor (Fraction)	0.92
Driver included	Yes	Connection	Connection unit 3-pole
Value ladder	Performance	Cable	Cable 0.25 m with connector 3-pole
		Protection class IEC	Safety class I
Light Technical		Controls and Dimming	
Luminous Flux	20,000 lm	Dimmable	Wireless Dim
Correlated Color Temperature (Nom)	6500 K	Driver/power unit/transformer	Sensor ready driver Interact System ready
Luminous Efficacy (rated) (Nom)	155.04 lm/W	Control interface	InterAct Pro
Color rendering index (CRI)	>80	Constant light output	No
		Maximum dim level	Programmable
Operating and Electrical		Mechanical and Housing	
Input Voltage	220 to 240 V	Housing Material	Aluminium
Line Frequency	50 or 60 Hz	Housing Color	White
Inrush current	5.1 A		
Inrush time	0.76 ms		

SlimPerform Batten

Mounting device	Mounting bracket
Overall length	1,691 mm
Overall width	59 mm
Overall height	82 mm
Dimensions (Height x Width x Depth)	82 x 59 x 1691 mm
Ingress protection code	IP20 [Finger-protected]
Net Weight (Piece)	2.500 kg

Approval and Application

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	60,000 hour(s)
---------------------------	----------------

Product Data

Order product name	BN310P LED200/865 SRD H4 HRO L1700 WH
Full product name	BN310P LED200/865 SRD H4 HRO L1700 WH
Order code	919406022091
Material Nr. (12NC)	919406022091
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400003265
Numerator - Packs per outer box	1
EAN/UPC - Case	17894400003262

Dimensional drawing

