



SlimPerform Batten

BN310P Bracket Black Spare Part

SlimPerform Batten, 0 W, 0 lm

Lighting plays a different role in every application. Some require latest-generation solutions with high light quality and connectivity; others just simple functionality. But whether for retail or industrial applications, you always need a combination of quality, performance, and flexibility. Get to know SlimPerform. The Batten LED luminaire where all these benefits come together. Putting the new lighting trend in your company.

Warnings and Safety

- 5-year warranty

Product data

General Information		Power Consumption	
Light source replaceable	No	Power Factor (Fraction)	0
Driver included	No	Connection	-
Value ladder	Performance	Cable	-
Light Technical		Protection class IEC	-
Luminous Flux	0 lm	Controls and Dimming	
Correlated Color Temperature (Nom)	-	Dimmable	No
Luminous Efficacy (rated) (Nom)	0 lm/W	Driver/power unit/transformer	-
Color rendering index (CRI)	-	Constant light output	No
Operating and Electrical		Mechanical and Housing	
Input Voltage	- V	Housing Material	Steel
Line Frequency	- Hz	Housing Color	Black
Inrush current	0 A	Overall height	68 mm
Inrush time	0 ms	Ingress protection code	-

