



DuraLED Well Glass

BY300P LED 35S WW PSU S1 PC

DuraLED well glass is designed to replace traditional Well Glass up to 70W with only 50% of the load for similar illumination. It is a perfect LED solution for outdoor application and industry of harsh condition like power plant, metal, and non-hazardous area in chemical and petrochemical industry. Compared to conventional HID Well Glass, it improves reliability, comfort, while reducing energy and maintenance cost dramatically. DuraLED Well Glass comes with 2 different mounting, Wall bracket (2 types) & Eye-bolt and comes with 2 color temperature and 2 lumen outputs.

Warnings and Safety

- Meant for use in Indoor Industrial environment only

Product data

General Information		Operating and Electrical	
Driver included	Yes	Input Voltage	120 to 277 V
Light source engine type	LED	Line Frequency	50 Hz
Warranty period	2 years	Power Consumption	33 W
		Power Factor (Fraction)	0.95
		Protection class IEC	Safety class I
		Surge Protection (Common/Differential)	Surge protection level until 4 kV
Light Technical		Controls and Dimming	
Luminous Flux	3,700 lm	Dimmable	No
Correlated Color Temperature (Nom)	3000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	120 lm/W		
Color rendering index (CRI)	>80	Mechanical and Housing	
Beam angle of light source	120 degree(s)	Housing Material	Aluminium pressure die cast
Light source color	830 warm white	Optic material	Polycarbonate
Optic type	Beam angle 120°	Optical cover material	Polycarbonate
Luminaire light beam spread	120°		

DuraLED Well Glass

Housing Color	Gray
Mounting device	Wall-mounting bracket
Material	Aluminum
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Opal diffuser in polycarbonate cover
Net Weight (Piece)	1.000 kg

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
Ambient temperature range	0 to +45 °C

Initial Performance (IEC Compliant)

Initial chromaticity	SDCM<5
----------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Product Data

Order product name	BY300P LED 35S WW PSU S1 PC
Full product name	BY300P LED 35S WW PSU S1 PC
Order code	919515812324
Material Nr. (12NC)	919515812324
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

