

Endura Next Batten

BN308C LED60S-4000 L120 PSU WH

With Philips Endura Next, customers have an industrial batten lighting solution that makes a valuable contribution to the profitability of their business, providing both operational and maintenance cost savings. By significantly reducing the energy consumption, this solution contributes to a lower carbon footprint. At the same time, the luminaire design ensures flicker free, consistent light output for the lifetime (50K hrs.), thereby guaranteeing the optimal working conditions for employees. It enhances productivity as well as takes care of safety of the employees. This unique solution comes with a wide range of intelligent (DALI, PIR movement detection) and networkable options such as Interact IoT enabled platform (both in Wired & Wireless options). No matter what your requirement is “Endura Next” comes with endless possibilities in this era of connected lighting and is specifically designed to minimize downtime in operations.

Warnings and Safety

- Meant for use in Indoor environment only

Product data

General Information	
Driver included	Yes
Light source engine type	LED
Warranty period	2 years

Light Technical	
Luminous Flux	6,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	120 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)
Light source color	840 neutral white

Optic type	Beam angle 120°
Luminaire light beam spread	120°

Operating and Electrical	
Input Voltage	140-270 V
Line Frequency	50 Hz
Power Consumption	47 W
Power Factor (Fraction)	0.95
Protection class IEC	Safety class I
Surge Protection (Common/Differential)	Surge protection level until 4 kV

Endura Next Batten

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	White
Mounting device	Surface & Suspended (Asymmetric/ Symmetric)
Material	Steel
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	Polycarbonate
Net Weight (Piece)	1.020 kg

Approval and Application	
Flammability mark	For mounting on normally flammable surfaces

Ambient temperature range	0 to +45 °C

Initial Performance (IEC Compliant)	
Initial chromaticity	<5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Median useful life L70B50	50,000 hour(s)

Product Data	
Order product name	BN308C LED60S-4000 L120 PSU WH
Full product name	BN308C LED60S-4000 L120 PSU WH
Order code	919515812667
Material Nr. (12NC)	919515812667
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.