



# DaySpace

## RC740B LED25S/865 W60L60 PSD WH

For the modern workspace lighting challenges that may inspire exciting new concepts or rejuvenate routine patterns, DaySpace offers a distinctive approach with the emphasis on the overall integrated look of the ceiling rather than on the luminaire itself. DaySpace discreetly integrates into the ceiling to deliver soft and ethereal yet brilliant environments. A luminous web or well-defined squares perched for a geometric yet whimsical space – DaySpace comes to your design rescue. For the Architects, Designers & Real Estate Professionals Designing/ Developing Next Gen Office Spaces DaySpace Provides. Creative Freedom to Blend in Lighting as an Architectural Element of the office. The opportunity to create the desired ambience through its customizable nature. To Declutter and break away from the Boring 2'x2' Lighting. Because of its unique design that minimizes the intrusion of the lighting surface into the office architecture and create a completely customized ambience

### Warnings and Safety

- Meant for Indoor Application Only. Should not be used in outdoor environment.

### Product data

General Information	
Driver included	Yes
Light source engine type	LED
Warranty period	3 years
Light Technical	
Luminous Flux	2,800 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)
Light source color	865 cool daylight

Optic type	Beam angle 120°
Luminaire light beam spread	120°
Operating and Electrical	
Input Voltage	120 to 277 V
Line Frequency	50 Hz
Power Consumption	30 W
Power Factor (Fraction)	0.9
Protection class IEC	Safety class I
Surge Protection (Common/Differential)	Surge protection level until 2.5 kV

## Controls and Dimming

Dimmable	Yes
Control interface	DALI

## Mechanical and Housing

Housing Material	Steel
Optic material	Polycarbonate
Optical cover material	Polystyrene
Housing Color	White RAL9016
Mounting device	Recessed mounting box square
Material	Steel
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	UV stabilized Polycarbonate cover
Net Weight (Piece)	3.500 kg

## Approval and Application

Flammability mark	For mounting on normally flammable surfaces
-------------------	---------------------------------------------

Ambient temperature range	0 to +45 °C
---------------------------	-------------

## Initial Performance (IEC Compliant)

Power consumption tolerance	+/-10%
-----------------------------	--------


## Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

## Product Data

Order product name	RC740B LED25S/865 W60L60 PSD WH
Full product name	RC740B LED25S/865 W60L60 PSD WH
Order code	919515813255
Material Nr. (12NC)	919515813255
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

## Dimensional drawing



Note - Actual product may differ from pictorial view.

