

# Sleek Surface PRO

## SM296C LED20S-4000 PSU WH

The Sleek SurfacePro family of downlights with bold and elegant metal delivers perfect balance of good design with high energy efficiency. It is a perfect solution for retail application and general indoor area lighting . The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design

### Warnings and Safety

- Meant for Indoor Application Only. Should not be used in outdoor environment.

### Product data

General Information		Power Factor (Fraction)	
Driver included	Yes		0.9
Light source engine type	LED	Protection class IEC	Safety class I
Warranty period	1 years	Surge Protection (Common/Differential)	2.5 kV kV
Light Technical		Controls and Dimming	
Luminous Flux	2,000 lm	Dimmable	No
Correlated Color Temperature (Nom)	4000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	110 lm/W	Mechanical and Housing	
Color rendering index (CRI)	>80	Housing Material	Aluminium pressure die cast
Beam angle of light source	- degree(s)	Optic material	Polycarbonate
Light source color	840 neutral white	Optical cover material	Polycarbonate
Optic type	-	Housing Color	Aluminum and gray
Luminaire light beam spread	-	Mounting device	Mounting bracket
Operating and Electrical		Optical cover shape	Flat
Input Voltage	220 to 240 V	Overall height	60 mm
Line Frequency	50 Hz	Overall diameter	153 mm
Power Consumption	18 W	Material	Pressure die cast aluminum
		Ingress protection code	IP20 [Finger-protected]

## Sleek Surface PRO

Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	Opal diffuser in polycarbonate cover
Net Weight (Piece)	0.380 kg

### Approval and Application

Flammability mark	For mounting on normally flammable surfaces
Ambient temperature range	0 to +45 °C

### Initial Performance (IEC Compliant)

Initial chromaticity	<5
Power consumption tolerance	+/-10%


### Over Time Performance (IEC Compliant)

Median useful life L70B50	30,000 hour(s)
---------------------------	----------------

### Product Data

Order product name	SM296C LED20S-4000 PSU WH
Full product name	SM296C LED20S-4000 PSU WH
Order code	919515814703
Material Nr. (12NC)	919515814703
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20

## Dimensional drawing



Type	Lumen Pack (lm)	Dimensions D x H (mm)	Voltage	Frequency	Kg
SM295C	600, 1000	Ø130 x 60	220-240V~	50Hz	0.45
SM296C	1200, 1500	Ø153 x 60	220-240V~	50Hz	0.55
SM296C	2000	Ø153 x 60	220-240V~	50Hz	0.40

