



Flat Line

SP570P LED26S 4000 PSD W12L120 OC SI

The Flat line family of luminaires gives you compromise-free office illumination with the sleek bar profile. It is a perfect solution for office application and general indoor area lighting. The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design.

Warnings and Safety

- Meant for Indoor Application Only. Should not be used in outdoor environment.

Product data

General Information		Power Consumption	
Driver included	Yes	Power Factor (Fraction)	0.95
Light source engine type	LED	Voltage (Nom)	120-277, 347 V
Warranty period	1 years	UL Type	TLED_Type A; UL listed HF
Light Technical		Protection class IEC	Safety class I
Upward light output ratio	0	Surge Protection (Common/Differential)	Surge protection level until 4 kV differential mode and 4 kV common mode
Luminous Flux	2,600 lm	Controls and Dimming	
Correlated Color Temperature (Nom)	6500 K	Dimmable	Yes
Luminous Efficacy (rated) (Nom)	115 lm/W	Control interface	DALI
Color rendering index (CRI)	>80	Mechanical and Housing	
Beam angle of light source	- degree(s)	Housing Material	Aluminum extruded
Light source color	840 neutral white	Optic material	Polycarbonate
Optic type	-	Optical cover material	Polycarbonate
Luminaire light beam spread	-	Housing Color	Silver
Unified glare rating CEN	19	Mounting device	Suspension set simple, standard
Operating and Electrical		Optical cover shape	-
Input Voltage	220 to 240 V	Overall length	1,200 mm
Line Frequency	50 Hz		

Flat Line

Overall width	120 mm
Overall height	33 mm
Dimensions (Height x Width x Depth)	33 x 120 x 1200 mm
Material	Aluminum
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	Opal prismatic cover
Net Weight (Piece)	2.700 kg

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
Ambient temperature range	0 to +45 °C

Initial Performance (IEC Compliant)

Initial chromaticity	<5
----------------------	----

Power consumption tolerance	+/-10%
-----------------------------	--------

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Product Data

Order product name	SP570P LED26S 4000 PSD W12L120 OC SI
Full product name	SP570P LED26S 4000 PSD W12L120 OC SI
Order code	919515814785
Material Nr. (12NC)	919515814785
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4

Dimensional drawing

