



Pureline slim

SP780X H LED22S-4000 PSU W5L112 OD WH

The PureLine Slim family of luminaires gives you compromise-free office illumination. It is a perfect solution for office application and general indoor area lighting with Sleek profile which helps Declutter the ceilings. The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design.

Warnings and Safety

- Meant for Indoor Application Only. Should not be used in outdoor environment.

Product data

General Information	
Driver included	Yes
Light source engine type	LED
Warranty period	1 years

Light Technical	
Luminous Flux	2,200 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	120 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	- degree(s)
Light source color	840 neutral white
Optic type	-
Luminaire light beam spread	-

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 Hz
Power Consumption	18 W

Power Factor (Fraction)	0.95
Protection class IEC	Safety class I
Surge Protection (Common/Differential)	Surge protection level until 4 kV

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Aluminum extruded
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	White
Mounting device	Suspension set simple, standard
Optical cover shape	Flat
Overall length	1,126 mm
Overall width	53 mm
Overall height	70 mm
Dimensions (Height x Width x Depth)	70 x 53 x 1126 mm

Pureline slim

Material	Aluminum
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	Polycarbonate Diffuser
Net Weight (Piece)	1.800 kg

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
Ambient temperature range	0 to +45 °C

Initial Performance (IEC Compliant)

Initial chromaticity	<5
Power consumption tolerance	+/-10%


Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Product Data

Order product name	SP780X H LED225-4000 PSU W5L112 OD WH
Full product name	SP780X H LED225-4000 PSU W5L112 OD WH
Order code	919515815255
Material Nr. (12NC)	919515815255
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4

Dimensional drawing



Type	Dimensions L x W x H, mm	Voltage	Frequency	Kg
SP780 H W5L112	1126 x 53 x 70	220-240V~	50Hz	1.9
SP780X H W5L112	1126 x 53 x 70	220-240V~	50Hz	1.9
SP780 H W5L168	1686 x 53 x 70	220-240V~	50Hz	2.6
SP780X H W5L168	1686 x 53 x 70	220-240V~	50Hz	2.6
SP780 H W5L224	2248 x 53 x 70	220-240V~	50Hz	3.8
SP780X H W5L224	2248 x 53 x 70	220-240V~	50Hz	3.8

