Standard Lustre P45 clear

Stan 40W E27 220-240V P45 CL 1CT/5X10F

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base

Product data

General Information	
Cap-Base	E27
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	385 lm
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45
Net Weight (Piece)	0.015 kg

Product Data	
Order product name	Stan 40W E27 220-240V P45 CL 1CT/5X10F
Full product name	Stan 40W E27 220-240V P45 CL 1CT/5X10F
Full product code	871829112414600
Order code	921421543301
Material Nr. (12NC)	921421543301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500223333
Numerator - Packs per outer box	50
EAN/UPC - Case	8718291124160

Standard Lustre P45 clear

Dimensional drawing



Product	D	C (max)
Stan 40W E27 220-240V P45 CL 1CT/5X10F	45 mm	73 mm

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.