



Standard Candle B35 clear

230V 25W CANDLE BC CLEAR

Flame-shaped bulb with clear glass and vacuum- or gas-filled bulb with B- or E-base

Product data

General Information	
Cap-Base	B22
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	205 lm
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	25 W
Voltage (Nom)	230 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	B35
Net Weight (Piece)	0.015 kg

Product Data	
Order product name	230V 25W CANDLE BC CLEAR
Full product name	230V 25W CANDLE BC CLEAR
Full product code	890143700285300
Order code	921485544299
Material Nr. (12NC)	921485544299
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8901437002853
Numerator - Packs per outer box	300
EAN/UPC - Case	8727900076516

Standard Candle B35 clear

Dimensional drawing



Product	D	C (max)
230V 25W CANDLE BC CLEAR	35 mm	94.5 mm

