

# Standard Candle B35 frosted

## 230V 25W BC PEARL CANDLE

Flame-shaped bulb with inside-frosted glass and vacuum- or gas-filled bulb with B- or E-base

### Product data

General Information	
Cap-Base	B22
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	205 lm
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	25 W
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	B35
Net Weight (Piece)	0.020 kg

Product Data	
Order product name	230V 25W BC PEARL CANDLE
Full product name	230V 25W BC PEARL CANDLE
Full product code	890143700286000
Order code	921485644299
Material Nr. (12NC)	921485644299
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8901437002860
Numerator - Packs per outer box	300
EAN/UPC - Case	8727900076523

## Standard Candle B35 frosted

### Dimensional drawing



Product	D	C (max)
230V 25W BC PEARL CANDLE	35 mm	95 mm

