



# Standard Candle B35 frosted

## Stan 40W E27 230V B35 FR 1CT/10X10F

Flame-shaped bulb with inside-frosted glass and vacuum- or gas-filled bulb with B- or E-base

### Product data

General Information	
Cap-Base	E27
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	390 lm
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	B35
Net Weight (Piece)	0.015 kg

Product Data	
Order product name	Stan 40W E27 230V B35 FR 1CT/10X10F
Full product name	Stan 40W E27 230V B35 FR 1CT/10X10F
Full product code	871150005646750
Order code	921492144218
Material Nr. (12NC)	921492144218
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500056467
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500168450

## Standard Candle B35 frosted

### Dimensional drawing



Product	D	C (max)
Stan 40W E27 230V B35 FR 1CT/10X10F	35 mm	96.5 mm

