



Standard Lustre P45 clear

40 W E27 cap 110-127 V Incandescent luster bulb

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base

Product data

General Information		Bulb Shape	
Cap-Base	E27	Bulb Shape	P45
Operating Position	UNIVERSAL [Any or Universal (U)]	Net Weight (Piece)	16.300 g
Nominal lifetime	1,000 hour(s)	Product Data	
Lighting Technology	Incandescent	Order product name	40 W E27 cap 110-127 V Incandescent luster bulb
Light Technical		Full product name	40 W E27 cap 110-127 V Incandescent luster bulb
Luminous Flux	455 lm	Full product code	789440000184100
Color rendering index (CRI)	100	Order code	923268735892
Operating and Electrical		Material Nr. (12NC)	923268735892
Power Consumption	40 W	Numerator - Quantity Per Pack	1
Starting Time (Nom)	0.0 s	EAN/UPC - Product/Case	7894400001841
Voltage (Nom)	127 V	Numerator - Packs per outer box	50
Mechanical and Housing		EAN/UPC - Case	7894400007966
Bulb Finish	Clear		

Standard Lustre P45 clear

Dimensional drawing

Product	D	C (max)
40 W E27 cap 110-127 V Incandescent luster bulb	45 mm	73 mm

