SPOTONE Ring Mirror Spotline

REF SPOT 40W E27 240V NR63 30DFR2CT/4X3F

Reflector lamps based on advanced spotlighting technology

Product data

General Information	
Cap-Base	E27
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Beam Angle (Nom)	30 degree(s)
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	240 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	NR63
Net Weight (Piece)	0.030 kg

Product Data	
Order product name	REF SPOT 40W E27 240V NR63 30DFR2CT/4X3F
Full product name	REF SPOT 40W E27 240V NR63 30DFR2CT/4X3F
Full product code	871150017130600
Order code	923339245520
Material Nr. (12NC)	923339245520
Numerator - Quantity Per Pack	2
EAN/UPC - Product/Case	8711500171306
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900844184

SPOTONE Ring Mirror Spotline

Dimensional drawing



Product	D
REF SPOT 40W E27 240V NR63 30DFR2CT/4X3F	63 mm

© 2026 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.