



Infrared Lamps Industrial Use

PAR38 IR 175W E27 230V CL 1CT/12

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, but also food. These benefits have made farmers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

Product data

General Information	
Cap-Base	E27
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	5,000 hour(s)
Rated Lifetime (Hours)	5,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Color Designation	C

Operating and Electrical	
Power Consumption	175 W
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	PAR38
Net Weight (Piece)	308.000 g

Product Data	
Order product name	PAR38 IR 175W E27 230V CL 1CT/12
Full product name	PAR38 IR 175W E27 230V CL 1CT/12
Full product code	871150011579915
Order code	923801344209
Material Nr. (12NC)	923801344209
Numerator - Quantity Per Pack	1

Infrared Lamps Industrial Use

EAN/UPC - Product/Case	8711500115799
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900207262

Dimensional drawing



Product	D	C (max)	C1 (max)
PAR38 IR 175W E27 230V CL 1CT/12	121 mm	136 mm	124 mm

