



Reflector Infrared BR40, PAR38

IR175R/PAR 120V 12/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Philips Infrared lamps are suited for heating and drying in industrial and commercial applications. These incandescent, gas-filled infrared heat lamps come up to full temperature almost immediately, eliminating costly warm-up time. Highly efficient heat generators that produce a minimum of light rays and a high amount of infrared radiation. The BR40 lamp provides a built-in reflector for radiant energy control.


Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	H45 [h45]
Nominal lifetime	5,000 hour(s)
Rated Lifetime (Hours)	5,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Color Designation	R
Operating and Electrical	
Power Consumption	175 W
Voltage (Nom)	115-125 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Red

Bulb Material	Hard Glass
Bulb Shape	PAR38
Net Weight (Piece)	308.000 g
Product Data	
Order product name	IR175R/PAR 120V 12/1
Full product name	IR175R/PAR 120V 12/1
Full product code	904667711627915
Order code	923813634608
Material Nr. (12NC)	923813634608
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677116279
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677232301

Reflector Infrared BR40,PAR38

Dimensional drawing



Product	D	C (max)	C1 (max)
IR175R/PAR 120V 12/1	121 mm	135 mm	123 mm

