Halogen non-reflector

7023 100W GY6.35 12V 1CT/10X10F

Low-voltage quartz halogen capsule lamps

Product data

General Information	
Cap-Base	GY6.35
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	50 h

Light Technical	
Correlated Color Temperature (Nom)	3450 K
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	100 W
Voltage (Nom)	12 V

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Net Weight (Piece)	0.003 kg

Approval and Application	
CE mark	Yes

Product Data	
Order product name	7023 100W GY6.35 12V 1CT/10X10F
Full product name	7023 100W GY6.35 12V 1CT/10X10F
Full product code	871150040981250
Local code description	7023
Order code	923870017103
Material Nr. (12NC)	923870017103
Local order code	7023
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500409812
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500423269

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
7023 100W GY6.35 12V 1CT/10X10F	11.5 mm	29.75 mm	30.25 mm	30 mm	1.30 mm	1.25 mm	1.20 mm	44 mm

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.