



Halogen non-reflector

7724I 100W GY6.35 12V

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.


Product data

General Information	
Cap-Base	GY6.35
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	2,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3100 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	100 W
Voltage (Nom)	12 V
Mechanical and Housing	
Bulb Material	Quartz-UV Open

Net Weight (Piece)	0.002 kg
Product Data	
Order product name	7724I 100W GY6.35 12V
Full product name	7724I 100W GY6.35 12V
Full product code	871150041280550
Order code	923875717103
Material Nr. (12NC)	923875717103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500412805
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500436603

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
7724I 100W	10.7 mm	29.65	30.25	30	1.30 mm	1.25	1.20 mm	44 mm
GY6.35 12V		mm	mm	mm		mm		

