



# Halogen reflector

## 13528 15W GZ4 6V 1CT/24

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.


### Product data

General Information		Mechanical and Housing	
Cap-Base	GZ4	Bulb Material	Quartz-UV Open
Operating Position	S105 [s105]	Reflector Finish	Smooth
Life to 50% Failures (Nom)	750 hour(s)	Bulb Shape	R35
		Net Weight (Piece)	12.000 g
Light Technical		Approval and Application	
Correlated Color Temperature (Nom)	2900 K	CE mark	Yes
Color rendering index (CRI)	100		
Operating and Electrical		Product Data	
Power Consumption	15 W	Order product name	13528 15W GZ4 6V 1CT/24
Voltage (Nom)	6 V	Full product name	13528 15W GZ4 6V 1CT/24
		Full product code	871869668993600
Controls and Dimming		Order code	923883810105
Dimmable	Yes	Material Nr. (12NC)	923883810105
		Numerator - Quantity Per Pack	1

## Halogen reflector

EAN/UPC - Product/Case	8718696689936
Numerator - Packs per outer box	24
EAN/UPC - Case	8718696689943

### Dimensional drawing



Product	D (max)	C (max)
13528 15W GZ4 6V 1CT/24	35 mm	42 mm

