



Halogen reflector

13163 250W GX5.3 24V 1CT/10X5F

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.


Product data

| General Information | | Mechanical and Housing | |
|-----------------------------|----------------------------------|-------------------------------|--------------------------------|
| Cap-Base | GX5.3 | Bulb Material | Quartz-UV Open |
| Operating Position | UNIVERSAL [Any or Universal (U)] | Reflector Finish | Smooth |
| Life to 50% Failures (Nom) | 50 hour(s) | Bulb Shape | R50 |
| | | Net Weight (Piece) | 0.024 kg |
| Light Technical | | Approval and Application | |
| Color rendering index (CRI) | 100 | CE mark | Yes |
| Operating and Electrical | | Product Data | |
| Power Consumption | 250 W | Order product name | 13163 250W GX5.3 24V 1CT/10X5F |
| Voltage (Nom) | 24 V | Full product name | 13163 250W GX5.3 24V 1CT/10X5F |
| Controls and Dimming | | Full product code | 871150040975160 |
| Dimmable | Yes | Order code | 923919720501 |
| | | Material Nr. (12NC) | 923919720501 |
| | | Numerator - Quantity Per Pack | 1 |

Halogen reflector

| | |
|---------------------------------|---------------|
| EAN/UPC - Product/Case | 8711500409751 |
| Numerator - Packs per outer box | 50 |
| EAN/UPC - Case | 8711500419415 |

Dimensional drawing



| Product | D (max) | C (max) |
|--------------------------------|---------|---------|
| 13163 250W GX5.3 24V 1CT/10X5F | 50 mm | 44.5 mm |

