



Halogen non-reflector

5761 30W G4 6V

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

Product data

General Information	
Cap-Base	G4
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	100 hour(s)

Light Technical	
Luminous Flux	765 lm
Correlated Color Temperature (Nom)	3200 K
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	30 W
Voltage (Nom)	6 V


Mechanical and Housing	
Bulb Material	Quartz-UV Open
Net Weight (Piece)	0.001 kg

Approval and Application	
CE mark	Yes

Product Data	
Order product name	5761 30W G4 6V
Full product name	5761 30W G4 6V
Full product code	871150041084950
Order code	923931110103
Material Nr. (12NC)	923931110103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410849
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500423344

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (max)	C (max)
5761 30W G4 6V	9.5 mm	19.75 mm	31 mm

