



Halogen non-reflector

5761 30W G4 6V

Low-voltage quartz halogen capsule lamps


Product data

General Information	
Cap-Base	G4
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	100 hour(s)
Light Technical	
Luminous Flux	765 lm
Correlated Color Temperature (Nom)	3200 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	30 W
Voltage (Nom)	6 V
Mechanical and Housing	
Bulb Material	Quartz-UV Open
Net Weight (Piece)	0.001 kg

Approval and Application	
CE mark	Yes
Product Data	
Order product name	5761 30W G4 6V
Full product name	5761 30W G4 6V
Full product code	871150041084950
Order code	923931110103
Material Nr. (12NC)	923931110103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410849
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500423344

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (max)	C (max)
5761 30W G4 6V	9.5 mm	19.75 mm	31 mm

