



Deco Tubular

7 W E14 cap Clear Incandescent tubular bulb

Tubular lamps with single- and coiled-coil filaments and clear, inside frosted or internally coated white bulbs with B- or E-base

Product data

General Information	
Cap-Base	E14
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	21 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	7 W
Lamp Current (Nom)	0.03 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230-240 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T17
Net Weight (Piece)	8.000 g

Approval and Application	
Energy Consumption kWh/1000 h	7 kWh
CE mark	Yes

Product Data	
Order product name	7 W E14 cap Clear Incandescent tubular bulb
Full product name	7 W E14 cap Clear Incandescent tubular bulb
Full product code	871150025008750
Order code	924151144441
Material Nr. (12NC)	924151144441
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500250087
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500251619

Deco Tubular

Dimensional drawing



Product	D (max)	C (max)
7 W E14 cap Clear Incandescent tubular bulb	17 mm	54 mm

