



Appliance Oven Tubular

App 15.4W E14 230-240V T22 CL OV 1CT

Tubular vacuum lamps with clear glass (T-bulb)

Product data

General Information	
Cap-Base	E14
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	90 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	15.0 W
Lamp Current (Nom)	0.06 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230-240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T22
Net Weight (Piece)	10.500 g
Approval and Application	
Energy Consumption kWh/1000 h	15 kWh
CE mark	Yes

Product Data	
Order product name	App 15.4W E14 230-240V T22 CL OV 1CT
Full product name	App 15.4W E14 230-240V T22 CL OV 1CT
Full product code	871150003659950
Order code	924196244441
Material Nr. (12NC)	924196244441
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500036599
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500257673

Appliance Oven Tubular

Dimensional drawing

Product	D (max)	C (max)
App 15.4W E14 230-240V T22 CL OV 1CT	22 mm	49 mm

