



Plusline Small

Plusline S 500W R7s 240V 1BC/12

Mains-voltage linear lamp giving white halogen light

Product data

General Information	
Cap-Base	R7s
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Luminous Flux	9,660 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	19.3 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	500 W
Lamp Current (Nom)	2.08 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	240 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3
Net Weight (Piece)	0.008 kg

Product Data	
Order product name	Plusline S 500W R7s 240V 1BC/12
Full product name	Plusline S 500W R7s 240V 1BC/12
Full product code	872790081918201
Order code	924735545501
Material Nr. (12NC)	924735545501
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900819182
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291225461

Plusline Small

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline S 500W R7s 240V 1BC/12	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm

