



DuraMax Deco Bent Tip

BC40BA9C/CL/LL 6/4

Philips DuraMax® Long Life Decorative bent tip bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Philips Duramax decorative bent tip bulbs are available in a variety of wattages with clear and frost finishes. The clear bulbs provide decorative sparkle, while the frost bulbs add a soft glow to add a pleasant touch to home decor.

Product data

General Information	
Cap-Base	E12 [Candelabra Screw]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	300 lm
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Shape	BA9
Net Weight (Piece)	0.010 kg
Product Data	
Order product name	BC40BA9C/CL/LL 6/4
Full product name	BC40BA9C/CL/LL 6/4
Order code	925251136317
Material Nr. (12NC)	925251136317
Numerator - Quantity Per Pack	4
EAN/UPC - Product/Case	046677168032
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677167207

DuraMax Deco Bent Tip

Dimensional drawing

Product

BC40BA9C/CL/LL 6/4

