



# Colors

## 60A/AGRO 120V 12/1

Philips Family of Colored A19 bulbs are ideal for holiday, party or special effects lighting.


### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	795 lm
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Softone Pink

Bulb Shape	A19
Net Weight (Piece)	0.032 kg
Product Data	
Order product name	60A/AGRO 120V 12/1
Full product name	60A/AGRO 120V 12/1
Order code	925279036306
Material Nr. (12NC)	925279036306
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677103163
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677151824

## Colors

### Dimensional drawing



A19

Product	D	C (max)
60A/AGRO 120V 12/1	2.375 inch	4.188 inch

