



# Essential LV MR16

## ESSPlus MR16 35W GU5.3 12V 36D 1CT/10x5F

The Essential LV MR16 is part of the Philips "Value for Money" ranges. It is a good choice for professional end-users looking for high-quality accent light to create contrast in shops, hotels and restaurants.


### Product data

General Information	
Cap-Base	GU5.3
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	3,000 hour(s)
Rated Lifetime (Hours)	3,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	36 degree(s)
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	35 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	MR16
Net Weight (Piece)	0.032 kg
Product Data	
Order product name	ESSPlus MR16 35W GU5.3 12V 36D 1CT/10x5F
Full product name	ESSPlus MR16 35W GU5.3 12V 36D 1CT/10x5F
Full product code	871829123047200
Order code	925711817102
Material Nr. (12NC)	925711817102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291230472
Numerator - Packs per outer box	50
EAN/UPC - Case	8718291230496

## Essential LV MR16

### Dimensional drawing



Product	D (max)	C (max)
ESSPlus MR16 35W GU5.3 12V 36D 1CT/10x5F	50.7 mm	46 mm

