



Standard Candle B35 frosted

Stan 40W E14 230V B35 FR 1CT/10X10F

Flame-shaped bulb with inside-frosted glass and vacuum- or gas-filled bulb with B- or E-base

Product data

General Information	
Cap-Base	E14
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	410 lm
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	230 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	B35
Net Weight (Piece)	0.015 kg

Product Data	
Order product name	Stan 40W E14 230V B35 FR 1CT/10X10F
Full product name	Stan 40W E14 230V B35 FR 1CT/10X10F
Full product code	871150001133650
Order code	926000006918
Material Nr. (12NC)	926000006918
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500011336
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500076748

Standard Candle B35 frosted

Dimensional drawing



Product	D	C (max)
Stan 40W E14 230V B35 FR 1CT/10X10F	35 mm	100 mm

