



# Standard Candle B35 frosted

## Stan 40W E14 230V B35 FR U 1CT/6X50CT


Flame-shaped bulb with inside-frosted glass and vacuum- or gas-filled bulb with B- or E-base

### Product data

General Information		Mechanical and Housing	
Cap-Base	E14	Bulb Finish	Frosted
Operating Position	UNIVERSAL [Any or Universal (U)]	Bulb Shape	B35
Nominal lifetime	1,000 hour(s)	Net Weight (Piece)	0.015 kg
Rated Lifetime (Hours)	1,000 hour(s)		
Lighting Technology	Incandescent		
Light Technical		Product Data	
Luminous Flux	410 lm	Order product name	Stan 40W E14 230V B35 FR U 1CT/6X50CT
Color rendering index (CRI)	100	Full product name	Stan 40W E14 230V B35 FR U 1CT/6X50CT
		Full product code	890143700485700
Operating and Electrical		Order code	926000205011
Power Consumption	40 W	Material Nr. (12NC)	926000205011
Voltage (Nom)	230 V	Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8901437004857
Controls and Dimming		Numerator - Packs per outer box	300
Dimmable	Yes	EAN/UPC - Case	8727900076981

## Standard Candle B35 frosted

### Dimensional drawing



Product	D	C (max)
Stan 40W E14 230V B35 FR U 1CT/6X50CT	35 mm	100 mm

