PHILIPS

Lighting

PL-C 2-PIN

PL-C 10W/827/2P 1CT/5X10BOX

PL-C new shape is an efficient and effective medium wattage fluorescent lamp, used in general downlights for retail, hospitality and office applications. The 2 PIN version is designed for electromagnetic gear and is provided with plug in/pull out lamp base. The 4 PIN version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G24d-1
Nominal lifetime	8,000 hour(s)

Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	600 lm
Color Designation	Incandescent White
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	60 lm/W
Color rendering index (CRI)	80

Operating and Electrical	
Power Consumption	10.4 W
Lamp Current (Nom)	190 mA

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	PL-C
Net Weight (Piece)	0.030 kg

PL-C 2-PIN

Approval and Application	
Mercury (Hg) Content (Nom)	1.3

Product Data	
Order product name	PL-C 10W/827/2P 1CT/5X10BOX
Full product name	PL-C 10W/827/2P 1CT/5X10BOX
Full product code	872016922512100
Order code	927812482701

Material Nr. (12NC)	927812482701
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169225121
Numerator - Packs per outer box	50
EAN/UPC - Case	8720169225145

Dimensional drawing



Product	D (max)	D1 (max)	A	B
PL-C 10W/827/2P 1CT/5X10BOX	26 mm	26 mm	84 mm	107.5 mm

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.