



PL-C 2-PIN

PL-C 18W/865/2P 1CT/5X10BOX

PL-C new shape is an efficient and effective medium wattage fluorescent lamp, used in general downlights for retail, hospitality and office applications. The 2 PIN version is designed for electromagnetic gear and is provided with plug in/pull out lamp base. The 4 PIN version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Color rendering index (CRI)	
Cap-Base	G24d-2		>80
Nominal lifetime	8,000 hour(s)	Operating and Electrical	
Light Technical		Power Consumption	18.3 W
Color Code	865 [CCT of 6500K]	Lamp Current (Nom)	220 mA
Luminous Flux	1,100 lm	Controls and Dimming	
Color Designation	Cool Daylight	Dimmable	No
Chromaticity Coordinate X (Nom)	313	Mechanical and Housing	
Chromaticity Coordinate Y (Nom)	337	Bulb Shape	PL-C
Correlated Color Temperature (Nom)	6500 K	Net Weight (Piece)	0.040 kg
Luminous Efficacy (rated) (Nom)	62 lm/W		

PL-C 2-PIN

Approval and Application


Mercury (Hg) Content (Nom)	1.3
----------------------------	-----

Product Data

Order product name	PL-C 18W/865/2P 1CT/5X10BOX
Full product name	PL-C 18W/865/2P 1CT/5X10BOX
Full product code	872016922746000
Order code	22746000

Material Nr. (12NC)	927812786501
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169227460
Numerator - Packs per outer box	50
EAN/UPC - Case	8720169227484

Dimensional drawing



Product	D (max)	D1 (max)	A	B
PL-C 18W/865/2P 1CT/5X10BOX	26 mm	26 mm	127.5 mm	150.5 mm

